

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adaptor

State: 22.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.



Features

Obj. č.	RX 9361.300
Výhody	Mounting on the busbar system and cable connection with just one screw
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 9005
Menovitý prúd (max.)	1 500 A
Menovitý prúd max.	1 500 A
Rated current of laminated copper bar	1 500 A
Rated current of laminated copper bar (UL)	1 380 A

Features

Elektrické parametre UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7
Vývod vodičov	Top/bottom
Pre prípojnicové systémy s rozstupom	60 mm
Počet pólov	Single-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 72,3 mm Výška: 119,4 mm Hĺbka: 117,4 mm
Priestor na upevnenie lamelových medených prípojnic (Š x V)	50 x 20 mm
Vhodné pre prípojnice	15 x 10 20 x 10 30 x 10
Rated voltage	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/EN 61439-1 UL 508
Menovité rázové napätie U _{imp}	12 kV
Rated insulation voltage U _i	1 000 V
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C

Features

Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Počet prípojok	2
Balenie	1 pc(s).
Netto hmotnosť	0,65 kg
Brutto hmotnosť	0,688 kg
PCF per pack (cradle-to-gate)	2,69
Číslo colnej sadzby	85369010
ETIM 9	EC001531
Popis výrobku	RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It boasts high levels of short-circuit protection and easy-to-fit contact hazard protection.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration