

Rittal – The System.

Faster – better – everywhere.



RX 9362.005

RiLineX NH fuse-switch disconnecter

State: 6.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.005 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



Features

Obj. č.	RX 9362.005
Prevedenie	s elektronickou indikáciou stavu poistiek (ESÜ) For 60 mm busbar systems s elektronickou indikáciou stavu poistiek (ESÜ)
Výhody	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94 Kontaktové dráhy: elektrolytická meď, postriebrená
Farba	RAL 9005 RAL 35745
Rozsah dodávky	Connectors for electronic fuse monitoring

Features

Pre prípojnicové systémy s rozstupom	60 mm
Vývod vodičov	Top/bottom
Spôsob (elektrického) pripojenia	Screw M8
Poistkové vložky	NH 00 NH 000
Menovité prevádzkové napätie	690 V AC
Pre veľkosť NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (poistkové vložky)
Rozmery	Šírka: 106 mm Výška: 229,5 mm Hĺbka: 104,5 mm
Rozsah prevádzkových teplôt	-5 °C...35 °C
Rozsah skladovacích teplôt	-25 °C...70 °C
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Vhodné pre prípojnicový systém	RiLineX RiLine60
Počet pólov	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Stupeň znečistenia	3
s elektronickou indikáciou stavu poistiek (ESÜ)	Yes
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Fire load	16,6 MJ/m ²

Features

Stratový výkon max.	19 W
Heat loss per fuse insert (max.)	12 W
Balenie	1 pc(s).
Netto hmotnosť	1,135 kg
Brutto hmotnosť	1,155 kg
Podiel medi (kg / ks)	0,363
PCF per pack (cradle-to-gate)	7,71
Číslo colnej sadzby	85369095
ETIM 9	EC001040
Popis výrobku	RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration