

# Rittal – The System.

Faster – better – everywhere.



## SV 9683.783

## Nosné rámy

State: 21.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9683.783 - Nosné rámy pre radové vstavané prístroje

Support frame set for accepting DIN rail-mounted devices (e.g. MCBs).

## Features

Obj. č.	SV 9683.783
Materiál	Nosný rám: ocelový plech, pozinkovaný, 1,5 mm Kryt: ocelový plech, lakovaný, 1,5 mm
Rozsah dodávky	Nosné lišty 2 montážne uholníky 1 kryt s výrezom Vrátane upevňovacieho materiálu
Pre výšku funkčného priestoru	300 mm
Vhodné pre	Šírka: = 800 mm
Počet deliacich jednotiek 17,5 mm	2 x 36
Balenie	1 pc(s).
Netto hmotnosť	4 kg
Brutto hmotnosť	4,3 kg
PCF per pack (cradle-to-gate)	16,4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	39269097
ETIM 9	EC002270
ECLASS 8.0	27400613
Popis výrobku	Nosný rám SV pre radovo vstavané zariadenia, 2 x 36 modulov, ŠxV: 700x295 mm, pre VX (Š: 800 mm)

## Approvals

# Approvals

---

Explanations

Declaration of conformity UK