


Rittal – The System.

Faster – better – everywhere.



SV 9340.860 Komplet kablov

State: 3.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.860 - Komplet kablov za OM adapterje z vzmetnim priključnim blokom

Predsestavljene priključni kabli za individualen priklop stikalnih naprav.



Features

Št. Modela	SV 9340.860
Opis izdelka	Predsestavljene priključni kabli za individualen priklop stikalne opreme, nameščene od zgoraj na OM adapterjih z vzmetnimi sponkami.
Material	PVC izolacija Temperaturno odporno do 105 °C Konci žic ultrazvočno zatesnjeni na obeh straneh
Opomba	AWG = American Wire Gauge
AWG	AWG12 = 3.31 mm ² ± 4 mm ²
Mere	Dolžina: 140 mm
Paketi	15 pc(s).
Neto teža	0,075 kg
Bruto teža	0,085 kg
Teža bakra (kg na kos)	0,003
Carinska tarifna številka	85444290
ETIM 9	EC000839
ECLASS 8.0	27062302
Opis izdelka	SV Cable set, AWG 12, L: 140 mm

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK