

Rittal – The System.

Faster – better – everywhere.



SV 9344.150 NH ločilnik

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9344.150 - NH ločilnik z elektromehanskim nadzorom varovalk

Features

Št. Modela	SV 9344.150
Zasnova	Za namestitev montažne plošče
Material	Poliamid Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	Ogrodje: RAL 7035 Pokrov: RAL 7035/7001
Vpenjalna površina za laminirane bakrene palice	Širina vpenjalnega območja: 32 mm Višina vpenjalnega območja: 10 mm
for mounting plate assembly	Yes
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M10
Nazivni obratovalni tok maks.	250 A
Nazivna delovna napetost	690 V, 3~
Za velikost NH	1
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 184 mm Višina: 298 mm
Priklop okroglih vodnikov	10 - 150 mm ²
Število polov	3-pole
Round conductor cross-section	10 - 150 mm ²
Paketi	1 pc(s).
Neto teža	2,599 kg

Features

Bruto teža	2,648 kg
Teža bakra (kg na kos)	0,3
Carinska tarifna številka	85369095
ETIM 9	EC000249
ECLASS 8.0	27371401
Opis izdelka	SV NH fuse-switch disconnecter, size 1, 250 A, 690 V, 3-pole, screw M10, with electromechanical fuse monitoring, for mounting plate assembly

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity Declaration of conformity UK