

Rittal – The System.

Faster – better – everywhere.



SV 9345.200 Fuse holders

State: 7.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9345.200 - Fuse holders 61 A to 400 A

3-pole, for busbar systems with 60 mm bar centre distance.

Features

Model No.	SV 9345.200
Design	For category J fuse type
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Electrolytic copper, silver-plated
Colour	Chassis: RAL 7035 Cover: RAL 7035/7001
Connection for round conductor	AWG 4/0 – MCM 600
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom
Type of electrical connection	Box terminal
For fuse type (class)	J
Rated operating current max.	200 A
Rated operating current (min.)	101 A
Rated operating voltage	600 V, 3~
Fuse standard	UL 248-8
Note	UL (listed accessory) is met when using the fuse holder on RiLine busbar systems
Standards	UL 508
Dimensions	Width: 210 mm Height: 288 mm
To fit fuses	Diameter: 41 mm Length: 146 mm
To fit busbars	Height: 5, 10 mm

Features

Electrical ratings UL (SCCR)	100 kA - 600 V, Fuse Class J max. 200 A, JDDZ/7
Number of poles	3-pole
Packs of	1 pc(s).
Net weight	3,939 kg
Gross weight	3,94 kg
Copper weight (kg per piece)	1,389
Customs tariff number	85369095
ETIM 9	EC001644
ECLASS 8.0	27400613
Product description	SV Fuse holder, Class J, 101-200 A, 600 V, 3-pole, (60 mm)

Approvals

Approvals	C-UR UL + C-UL (listed) UR + C-UR (recognized)
-----------	--

Tender text

Fuse holder Class J, 101 - 200 A, 3-pole
for busbar thickness 5 / 10 mm and PLS 800 / 1600
Type of connection
Box terminal, round conductor AWG 3/0 - MCM 600
System:
RiLine Class