

Rittal – The System.

Faster – better – everywhere.



RX 9360.500

RiLineX CB component adaptor

State: 18.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.500 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Features

Št. Modela	RX 9360.500
Zasnova	Easy Fix
Prednosti	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Obseg dobave	3 connection space covers
IP razred zaščite po IEC 60 529	IP 2XB
Nazivna impulzna vzdržna napetost Uimp	8 kV

Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage Ui	1.000 V
Rated impulse withstand current	80 kA
Stopnja kontaminacije	3
Število polov	3-pole
Kabelska vtičnica	Bottom
Vrsta električne povezave	Box terminal
Primerno za proizvajalca (tip)	ABB (A1, S2, T1, T2, XT1, XT2, FD63/FD160) BTicino (M1 160) Chint (NM8N-125, NM1-63H, NM1-125H, NXM-63S, NXM-125S, NXM-160S, NXMS-160) Eaton (NZM1) Fuji Electric (BW125JAG-3P) Hager (P160) Himel (HDM3-100F/N, HDM3L-125) Hyundai Electric (100AF, 125AF, 125D, 160D AF) Legrand (DPX 160, DPX 250 ER, DPX ³ 160) LS Electric (100AF, 125AF, TE100, TD100, TE160, TD160) Mitsubishi (NF63-SV, NF125-SV) OEZ (BC160) Rockwell (140G-C2C3-D10, 140G-C2C3-D12, 140-C2E3-D16, 140G-H0F3-D10, 140G-H0F3-D12, 140G-H0F3-D16) Sassin (3SM8L-100) Schneider (NSC100N, NSXm50, NSXm100, NSXm160, NSXm250, NSE100) Schrack (MC1) Siemens (3VA10, 3VA11) Terasaki (E125, S125)
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Osnovna frekvenca	50...60 Hz
Vlažnost okolice (brez kondenzacije)	10...90 %

Features

Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Delovno temperaturno območje	-25 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Mere	Širina: 82 mm Višina: 252 mm Globina: 63 mm
Paketi	1 pc(s).
Neto teža	1,364 kg
Bruto teža	1,367 kg
Teža bakra (kg na kos)	0,375
PCF na paket (od zibelke do vrat)	13,28
Carinska tarifna številka	85369095
ETIM 9	EC001531
Opis izdelka	RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration