

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.512

## RiLineX CB component adaptor

State: 27.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.512 - RiLineX CB component adaptor

This new product is currently unavailable. Alternatively, you can use the item number 9360.612.



## Features

Št. Modela	RX 9360.512
Zasnova	Easy Fix
Prednosti	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Obseg dobave	3 connection space covers
IP razred zaščite po IEC 60 529	IP 2XB
Nazivna impulzna vzdržna napetost $U_{imp}$	8 kV
Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage $U_i$	1.000 V

# Features

Stopnja kontaminacije	3
Vpenjalna površina za laminirane bakrene palice (Š x V)	15 x 6 mm
Število polov	3-pole
Kabelska vtičnica	Bottom
Vrsta električne povezave	Screw M8
Primerno za proizvajalca (tip)	ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW160_-3P, BW250_-3) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX <sup>3</sup> 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Sassin (3SM8N-225, 3SM8L-225) Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250)
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Osnovna frekvenca	50...60 Hz
Vlažnost okolice (brez kondenzacije)	10...90 %
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Delovno temperaturno območje	-25 °C...55 °C

# Features

Temperaturno območje shranjevanja	-25 °C...75 °C
Mere	Širina: 105 mm Višina: 252 mm Globina: 63 mm
Paketi	1 pc(s).
Neto teža	1,7 kg
Bruto teža	1,792 kg
Teža bakra (kg na kos)	0,608
PCF na paket (od zibelke do vrat)	10,84
Carinska tarifna številka	85369095
ETIM 9	EC001531
Opis izdelka	RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.

# Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration