

Rittal – The System.

Faster – better – everywhere.



RX 9360.535

RiLineX CB component adaptor

State: 8.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.535 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Št. Modela	RX 9360.535
Zasnova	Easy Fix
Prednosti	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Obseg dobave	3 terminal covers
IP razred zaščite po IEC 60 529	IP 2XB

Features

Nazivna impulzna vzdržna napetost U _{imp}	8 kV
Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage U _i	1.000 V
Stopnja kontaminacije	3
Število polov	3-pole
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M10
Prečni prerez	29 mm ² 6 mm ²
Primerno za proizvajalca (tip)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Osnovna frekvenca	50...60 Hz
Vlažnost okolice (brez kondenzacije)	10...90 %
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Delovno temperaturno območje	-25 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Mere	Širina: 145 mm Višina: 325,8 mm Globina: 76,4 mm
Fire load	22,239 MJ/m ²
Paketi	1 pc(s).
Neto teža	5 kg
Bruto teža	5,206 kg

Features

Teža bakra (kg na kos)	2,64
PCF na paket (od zibelke do vrat)	30,05
Carinska tarifna številka	85369095
ETIM 9	EC001531
Opis izdelka	RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. The cable outlet is easily converted to the top or bottom to suit individual requirements.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration