


**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.600**

**RiLineX CB component adaptor**

State: 10.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.600 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



## Features

Št. Modela	RX 9360.600
Zasnova	univerzalno
Prednosti	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Obseg dobave	3 connection space covers
IP razred zaščite po IEC 60 529	IP 2XB
Nazivna impulzna vzdržna napetost $U_{imp}$	8 kV

# Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage Ui	1.000 V
Stopnja kontaminacije	3
Število polov	3-pole
Kabelska vtičnica	Bottom
Prečni prerez	9 mm <sup>2</sup> 6 mm <sup>2</sup>
Primerno za proizvajalca (tip)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Osnovna frekvenca	50...60 Hz
Vlažnost okolice (brez kondenzacije)	10...90 %
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Delovno temperaturno območje	-25 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Mere	Širina: 81,9 mm Višina: 251,4 mm Globina: 50,8 mm
Paketi	1 pc(s).
Neto teža	0,92 kg
Bruto teža	1,22 kg
Teža bakra (kg na kos)	0,375
PCF na paket (od zibelke do vrat)	12,73
Carinska tarifna številka	85369095

# Features

---

ETIM 9	EC001531
--------	----------

---

Opis izdelka	RiLineX CB component adaptor (3-pole, max. 160 A) for 60 mm busbar systems. The device width is 81 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.
--------------	---

# Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------

---

Explanations	Declaration of conformity PCF-declaration
--------------	--