

Rittal – The System.

Faster – better – everywhere.



RX 9360.635

RiLineX CB component adaptor

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.635 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 145 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

Št. Modela	RX 9360.635
Zasnova	univerzalno
Prednosti	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005 RAL 35745
Obseg dobave	Including 3 connection space covers, 2 cross members and assembly parts
IP razred zaščite po IEC 60 529	IP 2XB

Features

Nazivna impulzna vzdržna napetost Uimp	8 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage Ui	1.000 V
Stopnja kontaminacije	3
Število polov	3-pole
Kabelska vtičnica	Top/bottom
Prečni prerez	29 mm ² 10 mm ²
Primerno za proizvajalca (tip)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Osnovna frekvenca	50...60 Hz
Vlažnost okolice (brez kondenzacije)	10...90 %
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Delovno temperaturno območje	-25 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Mere	Širina: 145 mm Višina: 325,8 mm Globina: 76,4 mm
Paketi	1 pc(s).
Neto teža	4,52 kg
Bruto teža	4,722 kg
Teža bakra (kg na kos)	2,64

Features

Carinska tarifna številka	85369095
ETIM 9	EC001531
Opis izdelka	RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. The cable outlet is easily converted to the top or bottom to suit individual requirements.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration