

Rittal – The System.

Faster – better – everywhere.



RX 9360.802

RiLineX bus-mounting fuse base

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.802 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.



Features

Št. Modela	RX 9360.802
Prednosti	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Product modification	(sekundarno)
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 35745 RAL 9005
Obseg dobave	4 bus-mounting fuse bases 12 reducers for D 01 fuses

Features

Vrsta električne povezave	Spring terminal
Maks. nazivni tok	63 A
Nazivna delovna napetost	400 V AC
Kabelska vtičnica	Bottom
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 26,8 mm Višina: 253,8 mm Globina: 89,8 mm
Priklop okroglih vodnikov	16 mm ²
Za namestitev zbiralnih sponk	Višina: 5, 10 mm
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	1.000 V
Izguba toplote maks.	5,5 W
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Vlažnost okolice (brez kondenzacije)	10...90 %
Utilisation category	AC-21B (400 V/100 A)

Features

Vložki varovalk	D 02-E 18
Paketi	4 pc(s).
Neto teža	1,432 kg
Bruto teža	1,437 kg
Teža bakra (kg na kos)	0,07
PCF na paket (od zibelke do vrat)	9,55
Carinska tarifna številka	85369095
ETIM 9	EC001644
Opis izdelka	RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm ² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--