

Rittal – The System.

Faster – better – everywhere.



RX 9360.824

RiLineX fuse-switch disconnecter

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.824 - RiLineX fuse-switch disconnecter D-Switch

RiLineX fuse-switch disconnecter for 60 mm busbar systems. For use with D 01 (via gauge ring) and D 02 slow fuses (max. 63 A). Also for use with 10 x 38 mm cylindrical fuses via the supplied retaining springs. Integral optical LED fuse monitoring plus electronic fuse monitoring with alarm contacts The switch is lockable in the on and off positions. Spring terminal blocks up to 16 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



Features

Št. Modela	RX 9360.824
Prednosti	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
General colour	RAL 35745 RAL 9005
Obseg dobave	4 fuse-switch disconnectors 12 reducers for D 01 fuses
Vrsta električne povezave	Spring terminal

Features

Maks. nazivni tok	63 A
Nazivna delovna napetost	400 V AC
Kabelska vtičnica	Bottom
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 35,8 mm Višina: 263 mm Globina: 104,2 mm
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	800 V
Izguba toplote maks.	5,5 W
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C
Vlažnost okolice (brez kondenzacije)	10...90 %
Utilisation category	AC-22B (400 V/100 A)
Vložki varovalk	D 02-E 18
Paketi	4 pc(s).
Neto teža	2,232 kg
Bruto teža	2,236 kg

Features

Teža bakra (kg na kos)	0,105
PCF na paket (od zibelke do vrat)	14,81
Carinska tarifna številka	85365080
ETIM 9	EC001040
Opis izdelka	RiLineX fuse-switch disconnecter for 60 mm busbar systems. For use with D 01 (via gauge ring) and D 02 slow fuses (max. 63 A). Also for use with 10 x 38 mm cylindrical fuses via the supplied retaining springs. Integral optical LED fuse monitoring plus electronic fuse monitoring with alarm contacts The switch is lockable in the on and off positions. Spring terminal blocks up to 16 mm ² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--