

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adaptor

State: 21.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.



Features

Št. Modela	RX 9361.300
Prednosti	Mounting on the busbar system and cable connection with just one screw
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94
Barva	RAL 9005
Nazivni tok (maks.)	1.500 A
Maks. nazivni tok	1.500 A
Rated current of laminated copper bar	1.500 A
Rated current of laminated copper bar (UL)	1.380 A

Features

Električne nazivne vrednosti UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7
Kabelska vtičnica	Top/bottom
Za sisteme palic z razmakom med središči	60 mm
Število polov	Single-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 72,3 mm Višina: 119,4 mm Globina: 117,4 mm
Vpenjalna površina za laminirane bakrene palice (Š x V)	50 x 20 mm
Za namestitev zbiralnih sponk	15 x 10 20 x 10 30 x 10
Rated voltage	1.000 V AC 1.500 V DC 600 V AC (UL) 600 V DC (UL)
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/EN 61439-1 UL 508
Nazivna impulzna vzdržna napetost U _{imp}	12 kV
Rated insulation voltage U _i	1.000 V
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C

Features

Temperaturno območje shranjevanja	-25 °C...75 °C
Vlažnost okolice (brez kondenzacije)	10...90 %
Število povezav	2
Paketi	1 pc(s).
Neto teža	0,65 kg
Bruto teža	0,688 kg
PCF na paket (od zibelke do vrat)	2,69
Carinska tarifna številka	85369010
ETIM 9	EC001531
Opis izdelka	RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It boasts high levels of short-circuit protection and easy-to-fit contact hazard protection.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration