

Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX connection adaptor

State: 5.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars.



Features

| | |
|---|---|
| Model No. | RX 9361.300 |
| Benefits | Mounting on the busbar system and cable connection with just one screw |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 |
| Rated current (max.) | 1.500 A |
| Rated current max. | 1.500 A |
| Rated current of laminated copper bar | 1.500 A |
| Rated current of laminated copper bar (UL) | 1.380 A |
| Electrical ratings UL (SCCR) | 52.5 kA - 600 V, RMS, unprotected 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 100 kA - 600 V, Fuse Class L max. 2000 A, JDDZ/7 |
| Cable outlet | Top/bottom |
| For bar systems with centre-to-centre spacing | 60 mm |

Features

| | |
|--|--|
| Number of poles | Single-pole |
| To fit busbar system | RiLineX RiLine60 |
| Dimensions | Width: 72.3 mm Height: 119.4 mm Depth: 117.4 mm |
| Clamping area for laminated copper bars (W x H) | 50 x 20 mm |
| To fit busbars | 15 x 10 20 x 10 30 x 10 |
| Rated voltage | 1.000 V AC 1.500 V DC 600 V AC (UL) 600 V DC (UL) |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Standards | IEC/EN 61439-1 UL 508 |
| Rated impulse withstand voltage U _{imp} | 12 kV |
| Rated insulation voltage U _i | 1.000 V |
| IP protection category to IEC 60 529 | IP 2XB |
| Maximum operating air humidity | 90 % |
| Operating temperature range | -5 °C...55 °C |
| Storage temperature range | -25 °C...75 °C |
| Ambient humidity (non-condensing) | 10...90 % |
| Number of connections | 2 |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---|
| Net weight | 0,65 kg |
| Gross weight | 0,688 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC001531 |
| Product description | RiLineX connection adaptor for 60 mm busbar systems. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars. |

Approvals

| | |
|--------------|--|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity PCF-declaration |

Tender text

RiLineX connection adaptor (1500 A)

RiLineX connection adaptor for 60 mm busbar systems. The device has screw fastening for simultaneous contact between the rail and conductor. For voltages up to 1000 V AC and 1500 V DC. IEC and UL approved.

Product information

Number of poles: 1

Busbar dimensions: 15/20/30 mm x 10 mm

Rated current max.: 1500 A

Connection: max. 1000 mm²

Cable outlet: oben/unten

Dimensions: 73 mm x 120 mm x 120 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9361300