

**Rittal – The System.**

Faster – better – everywhere.



**RX 9362.005**

**RiLineX NH fuse-switch  
disconnect**

State: 6.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.005 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



## Features

Št. Modela	RX 9362.005
Zasnova	z elektronskim nadzorom varovalk For 60 mm busbar systems z elektronskim nadzorom varovalk
Prednosti	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	RAL 9005 RAL 35745
Obseg dobave	Connectors for electronic fuse monitoring

# Features

Za sisteme palic z razmakom med središči	60 mm
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M8
Vložki varovalk	NH 00 NH 000
Nazivna delovna napetost	690 V AC
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 106 mm Višina: 229,5 mm Globina: 104,5 mm
Delovno temperaturno območje	-5 °C...35 °C
Temperaturno območje shranjevanja	-25 °C...70 °C
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Število polov	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Stopnja kontaminacije	3
z elektronskim nadzorom varovalk	Yes
IP razred zaščite po IEC 60 529	IP 2XB
Fire load	16,6 MJ/m <sup>2</sup>
Izguba toplote maks.	19 W

# Features

Heat loss per fuse insert (max.)	12 W
Paketi	1 pc(s).
Neto teža	1,135 kg
Bruto teža	1,155 kg
Teža bakra (kg na kos)	0,363
PCF na paket (od zibelke do vrat)	7,71
Carinska tarifna številka	85369095
ETIM 9	EC001040
Opis izdelka	RiLineX NH fuse-switch disconnecter in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.

# Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration