

Rittal – The System.

Faster – better – everywhere.



RX 9362.210

**RiLineX NH fuse-switch
disconnecter**

State: 11.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9362.210 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 2 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required.



Features

Št. Modela	RX 9362.210
Zasnova	For 60 mm busbar systems
Prednosti	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	RAL 9005 RAL 35745
Za sisteme palic z razmakom med središči	60 mm
Kabelska vtičnica	Top/bottom
Vrsta električne povezave	Screw M10
Vložki varovalk	NH 2
Nazivna delovna napetost	690 V AC

Features

Za velikost NH	2
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 208,5 mm Višina: 298,6 mm Globina: 134,6 mm
Delovno temperaturno območje	-5 °C...35 °C
Temperaturno območje shranjevanja	-25 °C...70 °C
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Število polov	3-pole
Stopnja kontaminacije	3
IP razred zaščite po IEC 60 529	IP 2XB
Fire load	46,16 MJ/m ²
Izguba toplote maks.	98 W
Paketi	1 pc(s).
Neto teža	3,87 kg
Bruto teža	3,942 kg
Teža bakra (kg na kos)	1,75
PCF na paket (od zibelke do vrat)	26,35
Carinska tarifna številka	85369095
ETIM 9	EC001040

Features

Opis izdelka

RiLineX NH fuse-switch disconnecter in size 2 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required.

Approvals

Approvals

CQC-CCC

Explanations

Declaration of conformity
PCF-declaration