

Rittal – The System.

Faster – better – everywhere.



RX 9363.035

RiLineX NH fuse-switch disconnecter

State: 5.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.035 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm². Includes electronic fuse monitoring.



Features

Št. Modela	RX 9363.035
Zasnova	Za namestitev montažne plošče
Prednosti	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko
Barva	RAL 9005 RAL 35745
Obseg dobave	Connectors for electronic fuse monitoring
for mounting plate assembly	Yes
Kabelska vtičnica	Top/bottom

Features

Vrsta električne povezave	Box terminal
Vložki varovalk	NH 00 NH 000
Rated insulation voltage U_i	1.000 kV
Nazivna delovna napetost	690 V AC
Za velikost NH	00
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke)
Mere	Širina: 106 mm Višina: 228,9 mm Globina: 86,1 mm
Priklop okroglih vodnikov	1,5 - 16 mm ²
Delovno temperaturno območje	-5 °C...35 °C
Temperaturno območje shranjevanja	-25 °C...70 °C
Število polov	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A)
Stopnja kontaminacije	3
z elektronskim nadzorom varovalk	Yes
IP razred zaščite po IEC 60 529	IP 2XB
Fire load	13,24 MJ/m ²
Priklop okroglih vodnikov, fina žica brez tulca	1,5 - 95 mm ²
Priklop okroglih vodnikov, fino pletenih z žičnimi tulci	1,5 - 95 mm ²
Round conductor cross-section	1,5 - 16 mm ²
Izguba toplote maks.	16 W

Features

Heat loss per fuse insert (max.)	12 W
Paketi	1 pc(s).
Neto teža	0,885 kg
Bruto teža	0,962 kg
Teža bakra (kg na kos)	0,268
PCF na paket (od zibelke do vrat)	5,98
Carinska tarifna številka	85369095
ETIM 9	EC001040
Opis izdelka	RiLineX NH fuse-switch disconnecter in size 00 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 95 mm ² . Includes electronic fuse monitoring.

Approvals

Approvals	CQC-CCC
Explanations	Declaration of conformity PCF-declaration