

# Rittal – The System.

Faster – better – everywhere.



## RX 9363.110

# RiLineX NH fuse-switch disconnecter

State: 21.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9363.110 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 1 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection.



## Features

|                             |   |
|-----------------------------|---|
| Št. Modela                  | RX 9363.110   |
| Zasnova                     | Za namestitev montažne plošče   |
| Prednosti                   | Cover: can be locked and prepared for a lead seal<br>Voltage test through separate opening<br>Tool-free changeover of the cable outlet<br>Park position for simpler maintenance work<br>All variants also available with electronic fuse monitoring |
| Material                    | Poliamid (PA 6)<br>Protipožarna zaščita v skladu z UL 94<br>Kontakti: elektrolitski baker s srebrno prevleko  |
| Barva                       | RAL 9005<br>RAL 35745   |
| for mounting plate assembly | Yes   |
| Kabelska vtičnica           | Top/bottom  |
| Vrsta električne povezave   | Screw M10   |
| Vložki varovalk             | NH 1  |
| Rated insulation voltage Ui | 1.000 kV  |
| Nazivna delovna napetost    | 690 V AC  |
| Za velikost NH              | 1   |

# Features

|                                   |  |
|-----------------------------------|--|
| Test specification                | IEC/DIN EN 60 947-3<br>DIN EN 60 269-2 (talilne varovalke)   |
| Mere                              | Širina: 181,8 mm<br>Višina: 298 mm<br>Globina: 110,5 mm  |
| Delovno temperaturno območje      | -5 °C...35 °C  |
| Temperaturno območje shranjevanja | -25 °C...70 °C   |
| Število polov                     | 3-pole   |
| Utilisation category              | AC-23B (400 V/100 A)<br>AC-22B (500 V/100 A)<br>AC-21B (690 V/100 A)<br>DC-22B (250 V/100 A)<br>DC-21B (440 V/100 A) |
| Stopnja kontaminacije             | 3  |
| IP razred zaščite po IEC 60 529   | IP 2XB   |
| Fire load                         | 33,55 MJ/m <sup>2</sup>  |
| Izguba toplote maks.              | 42 W   |
| Heat loss per fuse insert (max.)  | 23 W   |
| Paketi                            | 1 pc(s).   |
| Neto teža                         | 2,2 kg   |
| Bruto teža                        | 2,209 kg   |
| Teža bakra (kg na kos)            | 0,57   |
| PCF na paket (od zibelke do vrat) | 14,79  |
| Carinska tarifna številka         | 85369095   |
| ETIM 9                            | EC001040   |

# Features

---

Opis izdelka

RiLineX NH fuse-switch disconnecter in size 1 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection.

# Approvals

---

Approvals

CQC-CCC

Explanations

Declaration of conformity  
PCF-declaration