

Rittal – The System.

Faster – better – everywhere.



RX 9363.425

RiLineX NH fuse-switch disconnecter

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9363.425 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 000 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 50 mm². Includes electronic fuse monitoring.



Features

| | |
|-----------------------------|---|
| Št. Modela | RX 9363.425 |
| Zasnova | Za namestitev montažne plošče |
| Prednosti | Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring |
| Material | Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94 Kontakti: elektrolitski baker s srebrno prevleko |
| Barva | RAL 9005 RAL 35745 |
| Obseg dobave | Connectors for electronic fuse monitoring |
| for mounting plate assembly | Yes |
| Kabelska vtičnica | Top/bottom |

Features

| | |
|--|--|
| Vrsta električne povezave | Box terminal |
| Vložki varovalk | NH 000 |
| Rated insulation voltage Ui | 1.000 kV |
| Nazivna delovna napetost | 690 V AC |
| Za velikost NH | 000 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (talilne varovalke) |
| Mere | Širina: 53 mm Višina: 307,3 mm Globina: 80,1 mm |
| Priklop okroglih vodnikov | 1,5 - 16 mm ² |
| Delovno temperaturno območje | -5 °C...35 °C |
| Temperaturno območje shranjevanja | -25 °C...70 °C |
| Število polov | 3-pole |
| Utilisation category | AC-23B (400 V/100 A) AC-21B (500 V/100 A) AC-21B (690 V/100 A) DC-22B (250 V/100 A) |
| Stopnja kontaminacije | 3 |
| z elektronskim nadzorom varovalk | Yes |
| IP razred zaščite po IEC 60 529 | IP 2XB |
| Fire load | 9,69 MJ/m ² |
| Priklop okroglih vodnikov, fina žica brez tulca | 1,5 - 16 mm ² |
| Priklop okroglih vodnikov, fino pletenih z žičnimi tulci | 1,5 - 50 mm ² |
| Round conductor cross-section | 1,5 - 16 mm ² |
| Izguba toplote maks. | 26 W |
| Heat loss per fuse insert (max.) | 9 W |

Features

| | |
|-----------------------------------|--|
| Paketi | 1 pc(s). |
| Neto teža | 0,76 kg |
| Bruto teža | 0,779 kg |
| Teža bakra (kg na kos) | 0,26 |
| PCF na paket (od zibelke do vrat) | 5,49 |
| Carinska tarifna številka | 85369095 |
| ETIM 9 | EC001040 |
| Opis izdelka | RiLineX NH fuse-switch disconnecter in size 000 for mounting plates. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Box terminal connection to connect round conductors ranging from min. 1.5 to max. 50 mm ² . Includes electronic fuse monitoring. |

Approvals

| | |
|--------------|--|
| Approvals | CQC-CCC |
| Explanations | Declaration of conformity PCF-declaration |