

Rittal – The System.

Faster – better – everywhere.



RX 9364.024

RiLineX bus-mounting fuse base

State: 22.5.2026 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9364.024 - RiLineX bus-mounting fuse base

Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylindrical fuse 10 x 38 mm with electronic and optical LED fuse monitoring via alarm contacts. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 6 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



Features

Št. Modela	RX 9364.024
Prednosti	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Product modification	(sekundarno)
Material	Poliamid (PA 6) Protipožarna zaščita v skladu z UL 94-V0
Barva	RAL 35745 RAL 9005
Vrsta električne povezave	Spring terminal

Features

Maks. nazivni tok	32 A
Nazivna delovna napetost	400 V AC
Kabelska vtičnica	Bottom
Število polov	3-pole
Za namestitev sistema zbiralnih sponk	RiLineX RiLine60
Mere	Širina: 26,8 mm Višina: 262,5 mm Globina: 95 mm
Priklop okroglih vodnikov, fino pletenih z žičnimi tulci	1,5 - 6 mm ²
Priklop okroglih vodnikov, fina žica z AWG končnim tulcem	AWG 16 - AWG 6
Priklop okroglih vodnikov, večžični	1,5 - 6 mm ²
Priklop okroglih vodnikov, večžilnih mm ²	AWG 16 - AWG 10
Za namestitev zbiralnih sponk	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Kategorija prenapetosti	4
Stopnja kontaminacije	3
Standardi	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	800 V
Izguba toplote maks.	3 W
IP razred zaščite po IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Delovno temperaturno območje	-5 °C...55 °C
Temperaturno območje shranjevanja	-25 °C...75 °C

Features

Vlažnost okolice (brez kondenzacije)	10...90 %
Utilisation category	AC-20B (400 V/100 A)
Vložki varovalk	10 x 38 mm
Paketi	4 pc(s).
Neto teža	1,4 kg
Bruto teža	1,412 kg
Teža bakra (kg na kos)	0,043
PCF na paket (od zibelke do vrat)	9,36
Carinska tarifna številka	85369095
ETIM 9	EC001644
Opis izdelka	Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylindrical fuse 10 x 38 mm with electronic and optical LED fuse monitoring via alarm contacts. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 16 mm ² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--