

Rittal – The System.

Faster – better – everywhere.



SV 9661.230

PE/PEN combination angle E-Cu

State: 5.9.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9661.230 - PE/PEN combination angle E-Cu for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Features

Model No.	SV 9661.230
Product description	The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.
Benefits	Thanks to the pre-assembled combination angles, baying brackets and busbars customised to match the enclosure width, assembly is time-saving with cost reduction
Applications	Form 2-4 Other
Material	E-Cu
Supply includes	Assembly parts
Approved short-circuit current capability	I _{cw} 30 kA, 1 sec.
To fit busbars	Busbar E-Cu with integral punchings
OUT_CROSS_SECTION_COL_SM	30 - 10 mm
To fit busbars	Width: 30 Height: 10 mm
Packs of	4 pc(s).
Net weight	2
Gross weight	2.177
Copper weight (kg per piece)	0.39
Customs tariff number	74198090
EAN	4028177546653

Features

ETIM 9	EC000329
ECLASS 8.0	27400605

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---