

Rittal – The System.

Faster – better – everywhere.



SV 9677.810

Tokovni transformator

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.810 - Tokovni transformator

Za induktivno merjenje pretoka toka.

Features

Št. Modela	SV 9677.810
Opis izdelka	Kompaktna zasnova brez spreminjanja globine vgradnje zaradi mehanske integracije v komponente (medosna razdalja 185 mm) omogoča zasnovo, ki prihrani prostor.
Material	Poliamid
Za velikost	00
Za model št.	9677.000 9677.010 9677.015 9677.025 9677.060 9677.065 9677.070 9677.075 9677.080 9677.085
Nazivna vhodna moč	2,5 VA
Vrsta električne povezave	Screw terminals
Insulation material (class)	E
Primary current	150 A
Secondary current	5 A
Accuracy Class	1
Test specification	IEC 60 044-1 EN 60715 DIN VDE 0414 DIN 42 600-2
Priklop okroglih vodnikov	2,5 - 4 mm ²

Features

Nazivna frekvenca	50 - 60 Hz
Paketi	1 pc(s).
Neto teža	0,2 kg
Bruto teža	0,21 kg
Carinska tarifna številka	85043129
ETIM 9	EC002048
ECLASS 8.0	27141146
Opis izdelka	SV Current transformer, for, NH slimline fuse-switch disconnecter/, NH slimline switch-disconnector, size 00 (SV 9677XXX)

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---