

Rittal – The System.

Faster – better – everywhere.



VX 9680.808

Bayed enclosure system VX25

State: 6.2.2026 (Source: ittal.com/si-sl)



FRIEDHELM LOH GROUP

VX 9680.808 - Bayed enclosure system VX25 Modular enclosure

Baying systems VX, for installation with partial doors and internal separation in a modular design.

Features

Model No.	VX 9680.808
Material	Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure frame Rear panel Gland plates
Protection category to IEC 60 529	Up to IP 54, depending on the panels
Test specification	IEC 61 439-1/-2 IEC 61 641
Dimensions	Width: 800 mm Height: 2,000 mm Depth: 800 mm
Packs of	1 pc(s).
Net weight	49.54
Gross weight	63.6
PCF per pack (cradle-to-gate)	158.2 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
EAN	4028177929555
ETIM 9	EC000261

Features

ECLASS 8.0

27180101

Approvals

Certificates

Surface finish

Explanations

Declaration of conformity UK