

Rittal – The System.

Faster – better – everywhere.



SR 2347.235

Swing frame, large, with trim panel

State: 24.03.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2347.235 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.



Features

Model No.	SR 2347.235
Design	482.6 mm (19") level, centre
Product description	For mounting 482.6 mm (19") equipment.
Material	Sheet steel
Surface finish	Frame: Zinc-plated Trim panel: Spray-finished
Colour	RAL 7035
Supply includes	Locking rod system with double-bit lock insert Material for attaching
Installation options	In the TS/SE with 180° opening angle
Assembly instruction	Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required

Features

Note	For further installation options, see "Technical details" For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock
To fit	Enclosure type: TS VX SE Width: = 800 mm Height: ≥ 2,200 mm
Units	45 U
To fit enclosure type	TS VX SE
Packs of	1 pc(s).
Net weight	22.462 kg
Gross weight	23.644 kg
Customs tariff number	94039910
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	SR Swing frame, large, with trim panel, for TS, VX SE, for W: 800 mm, 45 U, installed at the centre

Tender text

Large swing frame for network enclosure

45 U can be used for accommodating 482.6 mm (19") equipment.

Torsionally stiff frame, welded from rectangular tube and triple folded support section. Load capacity up to 1500 N when standard hinges are used. Distance from inside edge of door to front edge of swing frame 100 mm, may be installed deeper on a pitch pattern of 25 mm. The swing frame must be fitted to the left / to the right depending on the installation depth of the equipment.

Installation position of equipment mounted in the centre.

Material: sheet steel

Surface finish: RAL 7035

for enclosure width: W: 800 mm