

Rittal – The System.

Faster – better – everywhere.



SK 3144.000

Tlačné ventilátory pre 482,6 mm (19")

State: 2.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3144.000 - Tlačné ventilátory pre 482,6 mm (19")

Množstvo vzduchu 320 m³/h

2 U tangential fan with up to 320 m³/h air throughput. The minimal noise generation of 52 dB makes it suitable for use in office environments.

Features

Obj. č.	SK 3144.000
Farba	RAL 9005
Rozsah dodávky	Kompletné zariadenie pripravené na okamžité pripojenie a použitie Filtrovaná vložka
Počet otáčok	2 245 rpm
Menovité prevádzkové napätie	230 V, 1~, 50 Hz/60 Hz
Menovitý elektrický príkon Pel	Pri 50 Hz: 37 W Pri 60 Hz: 46 W
Menovitý prúd max.	Pri 50 Hz: 0,16 A Pri 60 Hz: 0,22 A
Rozmery	Šírka: 482,6 mm Výška: 88 mm Hĺbka: 163 mm
Hladina akustického tlaku	Pri 50 Hz: 52 dB(A) Pri 60 Hz: 62 dB(A)
Max. statický rozdiel tlakov	65 - 70 Pa
Rozsah prevádzkových teplôt	-10 °C...55 °C
Vnútorý okruh pri 50 Hz	320 m ³ /h
Vnútorý okruh pri 60 Hz	330 m ³ /h
Balenie	1 pc(s).
Netto hmotnosť	2,2 kg
Brutto hmotnosť	2,4 kg
Číslo colnej sadzby	84145915

Features

ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716
Popis výrobku	SK radiálny ventilátor, pre 482,6 mm (19"), 320 m ³ /h, 230 V, 50/60 Hz, ŠxVxH: 482,6 x 88 x 158 mm

Approvals

Explanations

Declaration of conformity