


Rittal – The System.

Faster – better – everywhere.



SK 3311.380

Kondenzátorová jednotka

State: 5.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3311.380 - Kondenzátorová jednotka pre LCP DX

The condenser units are necessary for operating refrigerant-based LCPs. Depending on the version, the units have an external condenser and fan, or additionally a free cooler. The variant with free cooler is needed for the combination variant LCP DX/FC. The units are suitable for roof and wall mounting.



Features

Obj. č.	SK 3311.380
Prevedenie	Kondenzátor so systémom voľného chladenia
Materiál	Oceľový plech, s nástrekom
Povrch	Štruktúrovaná prášková farba, pozinkované
Farba	RAL 9003
Rozsah dodávky	Základná jednotka a oddelený kondenzátor Vrátane montážneho materiálu
Max. chladiaci výkon	35 kW
Regulácia teploty	Speed-controlled fan
Chladiace médium/chladivo	Chladivo: R410A Chladiace médium: Water/glycol
Rozmery	Šírka: 3.048 mm Výška: 1.270 mm Hĺbka: 1.100 mm
Celkový chladiaci výkon / počet ventilátorov	2
Menovité prevádzkové napätie	400 V, 3~, 50 Hz/60 Hz

Features

Balenie	1 pc(s).
Netto hmotnosť	235 kg
Brutto hmotnosť	290 kg
Číslo colnej sadzby	84189910
ETIM 9	EC002515
ETIM 8	EC002515
ECLASS 8.0	27180712
Popis výrobku	Vzduchom chladený hybridný kondenzátor pre LCP Inline DX/FC 35kW, pre montáž na strechu/stenu, napájanie: 400V, 3~, 50/60 Hz, ŠxVxH: 3048x1270x1110 mm, RAL 9003