


Rittal – The System.

Faster – better – everywhere.



SZ 2411.140 EMC cable glands

State: 12.03.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.140 - EMC cable glands

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

Model No.	SZ 2411.140
Design	Cable glands, PG
Product description	The cable sheathing may optionally be interrupted at the contact point or removed completely inside the enclosure. The cable shielding in the enclosure is retained. The supplied lock nut cuts automatically into the paint when screwed onto spray-finished enclosure surfaces, thus creating a conductive connection.
Material	Brass Seal: CR/NBR
Surface finish	Nickel-plated
Note	Minimum shield diameter = cable diameter less cable sheathing
Min. cable diameter	6 mm
Max. cable diameter	12 mm
Protection category IP 69K	IP 69K
IP protection category to IEC 60529	IP 68
Shield diameter (min.)	5 mm
Packs of	5 pc(s).
Net weight	0.175 kg
Gross weight	0.181 kg
Customs tariff number	73269098
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

Explanations

Declaration of conformity