

Rittal – The System.

Faster – better – everywhere.



AS 4050.060

Upínací rám

State: 25.6.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.060 - Upínací rám

Parallel machining of enclosures in the cube machining zone of Perforex machining centres BC and Perforex milling terminals MT for shorter setup times and enhanced productivity.

Features

Obj. č.	AS 4050.060
Prevedenie	Pneumatické upínacie zariadenie
Possible number of terminal Boxes for parallel processing	3
Poznámka	Použitie upínacieho rámu (obj. č. 4050.080) pri obrábacom centre BC (obj. č. 4050.230) je možné iba pri dvojdverovom variante.
Vhodný pre obj. č.	4050.101 4055.910 4055.911
Suitable for	Perforex BC 1001 HS Perforex MT 1101 Perforex MT 1101 S
Rozmery upnutelných kompaktných skriň max.	Šírka: 200 mm Výška: 300 mm Hĺbka: 300 mm
Rozmery upnutelných kompaktných skriň min.	Šírka: 85 mm Výška: 70 mm Hĺbka: 70 mm
Balenie	1 pc(s).
Netto hmotnosť	25 kg
Brutto hmotnosť	25 kg
Číslo colnej sadzby	84669360
ETIM 9	EC003010
ETIM 8	EC003010
ECLASS 8.0	36609190

Features

Popis výrobku

Upevňovací rám BC 1001, kompakt min. 85x70x70 / max.
200x300x300mm,