


Rittal – The System.

Faster – better – everywhere.



AS 4050.437

Ručné strihacie zariadenie DIN líšt - MC3

State: 2.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.437 - Ručné strihacie zariadenie DIN líšt - MC3

Manual profile cutter for cutting C rails 30/15 and support rails TS 35/7.5 and TS 35/15 to length, burr-free. The desired rail length can be set precisely and reproducibly using the ruler (mm/inch) and the adjustable end stop. For mounting on the workbench.



Features

Obj. č.	AS 4050.437
Výhody	Cenovo výhodné ručné rezanie profilových a nosných líšt Uľahčuje rezanie DIN líšt oproti ručnému skracovaniu Skracovanie bez otrepov s excentrickou pákou bez vynakladania veľkej sily Nevyžaduje údržbu a má dlhú životnosť
Využitelná plocha	Šírka: 1.343 mm Výška: 1.162 mm Hĺbka: 312 mm
Obrobiteľný materiál	Sheet steel Aluminium Copper
Balenie	1 pc(s).
Netto hmotnosť	15 kg
Brutto hmotnosť	16,15 kg
Číslo colnej sadzby	73269098
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	36600890

Features

Popis výrobku

Na rezanie železa, medi a hliníka do hrúbky 1,2 mm, plastu do hrúbky 2,0 mm, šírka rezu 2,7 mm