


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.456 Krimpovací stroj RC

State: 21.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.456 - Krimpovací stroj RC

Electropneumatic crimping machine with 5-way magazine for processing insulated wire end ferrules in various cross-sections on a reel.



## Features

Obj. č.	AS 4050.456
Prevedenie	Dotykový displej Výber prierezu kábla pomocou dotykovej obrazovky Držiak je možné osadiť max. 23 000 izolovanými dutinkami
Výhody	Jednoduchá prevádzka Bezpečné a plynulé spracovanie izolovaných dutiniek Proces bez potreby výmeny nástrojov Jednoduché a plynulé osadzovanie Vďaka päťnásobnému osadeniu nie je nutná výmena izolovaných dutiniek
Technické údaje	Rozsah krimpovania 0,5 – 2,5 mm <sup>2</sup> (AWG 20 – 14) Krimpovacia dĺžka 8 a 10 mm Zavádzacia dĺžka 27 mm (1,06 in.)
Poznámka	Štandardný krimpovací tvar lichobežník – ďalší na požiadanie
Rozmery	Šírka: 335 mm Výška: 565 mm Hĺbka: 485 mm
Prípojka stlačeného vzduchu	5,5 bar
Menovité prevádzkové napätie	100 V - 240 V, 1~, 50 Hz/60 Hz
Elektrický príkon	16 VA
Lisovanie	Trapezoid crimp

# Features

Pracovný cyklus	2 s
Balenie	1 pc(s).
Netto hmotnosť	24,8 kg
Brutto hmotnosť	25,4 kg
Číslo colnej sadzby	84624900
ETIM 9	EC002778
ETIM 8	EC002778
ECLASS 8.0	17130101
Popis výrobku	Krimpovací stroj RC, odizolovanie a krimpovanie, na spracovanie 5 kotúčov s dutinkami