

**Rittal – The System.**

Faster – better – everywhere.



**DK 5302.202**

**Panel na pretiahnutie káblov s  
kefovou lištou**

State: 7.7.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.202 - Panel na pretiahnutie káblov s kefovou lištou 482,6 mm (19")

With cut-out 390 x 60 mm when using two opposite panels (2 U) or 390 x 30 mm for one panel (1 U) with brush insert.



## Features

Obj. č.	DK 5302.202
Výhody	Pre zväčšenie káblovej priechodky je možné jednoducho vzájomne kombinovať dva panely
Oblasti použitia	Na uzavretie káblového vedenia a súčasného káblového vedenia v priestore montáže v 1 U, 482,6 mm (19") montážny štandard
Materiál	Oceľový plech Kefová lišta: plast, UL 94-HB, bez obsahu halogénu Vláčna kefovej lišty: plast PA6, bez obsahu halogénu Upevňovací korpus kefovej lišty: plast PVC, obsahujúci halogény
Povrch	S nástrekom
Farba	RAL 9005
Montážny výrez	Šírka:390 mm Výška:30 mm
Rozmery	Šírka: 482,6 mm
Výškové moduly	1 U
Balenie	1 pc(s).
Netto hmotnosť	0,2 kg
Brutto hmotnosť	0,243 kg

# Features

PCF per pack (cradle-to-gate)	0,9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604
Popis výrobku	Káblový vstup s kefovou lištou, 1 U, 482,6 mm (19"), ocelový plech, RAL 9005