


Rittal – The System.

Faster – better – everywhere.



VX 8840.100

System radových skříň VX25

State: 30.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8840.100 - Systém radových skříň VX25 Základná skriňa s presklenými dverami

The VX basic enclosure with glazed door for industrial applications: Enclosure frame with glazed door at the front, rear door, roof plate, divided gland plates. Perfectly suited to efficient enclosure interior installation.



Features

Obj. č.	VX 8840.100
Materiál	Rámová konštrukcia skrine: ocelový plech, 1,5 mm Strecha: ocelový plech 1,5 mm Presklené dvere: jednovrstvové bezpečnostné sklo, 3 mm Zadné dvere: Ocelový plech, 2,0 mm Podlahové plechy: ocelový plech 1,5 mm
Povrch	Rámová konštrukcia skrine: základná farba nanosená máčaním Dvere, strecha a zadná stena: základná farba nanosená máčaním, z vonkajšej strany štruktúrovaná prášková farba
Farba	RAL 7035
Rozsah dodávky	Rámová konštrukcia skrine Predné presklené dvere s hliníkovým rámom (180°) Dvere z ocelového plechu vzadu (130°) Predný a zadný uzáver: 3 mm, Doppelbart Strešný plech Podlahový plech

Features

Rozmery	Šírka: 800 mm Výška: 2.000 mm Hĺbka: 600 mm
Stupeň krytia IP podľa normy EN 60 529	IP 55
Stupeň krytia NEMA	NEMA 1 NEMA 12
Type rating podľa UL 50E	Type 1 Type 12
Kód IK	IK08
Základný materiál	Sheet steel
Balenie	1 pc(s).
Netto hmotnosť	82 kg
Brutto hmotnosť	84,2 kg
PCF per pack (cradle-to-gate)	207,5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Popis výrobku	Systém radovo spojených skriň VX, ŠxVxH: 800x2000x600 mm, oceľový plech, bez montážnej dosky, presklené dvere na prednej strane

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish Protection category

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK