

Rittal – The System.

Faster – better – everywhere.



RX 9360.210

RiLineX connection adaptor

State: 21.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.210 - RiLineX connection adaptor

RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.



Features

Obj. č.	RX 9360.210
Výhody	Mounting on the busbar system and cable connection with just one screw
Materiál	Polyamid (PA 6) Ochrana proti požiaru zodpovedá UL 94
Farba	RAL 9005
Menovitý prúd (max.)	171 A
Menovitý prúd max.	320 A
Rated current of round conductor	320 A
Rated current of round conductor (UL)	280 A
Elektrické parametre UL (SCCR)	10 kA - 600 V, RMS 100 kA - 600 V, circuit breaker max. 250 A, DIVQ/7 100 kA - 600 V, Fuse Class J max. 200 A, JDDZ/7
Vývod vodičov	Top/bottom

Features

Pre prípojnicové systémy s rozstupom	60 mm
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 63,2 mm Výška: 239,4 mm Hĺbka: 79,2 mm
Pripojenie okrúhlych vodičov	2,5 - 70 mm ²
Priestor na upevnenie lamelových medených prípojnic (Š x V)	13 x 5 mm
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	800 V AC 800 V DC 600 V AC (UL) 600 V DC (UL)
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/EN 61439-1 UL 508
Menovité rázové napätie U _{imp}	8 kV
Rated insulation voltage U _i	800 V
Stratový výkon max.	14 W
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %

Features

Balenie	4 pc(s).
Netto hmotnosť	1,776 kg
Brutto hmotnosť	1,925 kg
PCF per pack (cradle-to-gate)	9,86
Číslo colnej sadzby	85369010
ETIM 9	EC001531
Popis výrobku	<p>RiLineX connection adaptor for 60 mm busbar systems. The adaptor boasts an impressive compact design and simple conductor connection. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support through-wiring. Mounted by simply snapping onto the RiLineX board. The supply leads and adaptors are screw-fastened onto the board together. The connection adaptor features a high current-carrying capacity plus high levels of short-circuit protection and universal contact hazard protection that adapts to the relevant wire gauge. The device has a screw fastening, and is suitable for bar widths of between 5 and 10 mm.</p>

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration