


# Rittal – The System.

Faster – better – everywhere.



## SV 3052.000 Busbar support

State: 17.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3052.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



## Features

Model No.	SV 3052.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole 185 mm
To fit busbars	50 x 10 60 x 10 80 x 10
Rated current max.	1,600 A
Note on Model No.	The base component of the busbar support may also be used as a single-pole support.
Dimensions	Width: 24 mm Height: 515 mm Depth: 51 mm
Packs of	2 pc(s).
Net weight	1.26
Gross weight	1.338
Customs tariff number	85369010
EAN	4028177035751

## Features

ETIM 9	EC001166
ETIM 8	EC001166
ECLASS 8.0	27400607

## Approvals

Approvals	ABS
Explanations	Declaration of conformity Declaration of conformity UK

## Tender text

SV busbar support  
for accommodating busbars. 3-pole busbar support  
with 185 mm bar centre distance.  
Suitable for busbars from 50 x 10 mm to 80 x 10 mm  
with inserts.

Rated operating voltage: 1000 V~, 50/60 Hz to VDE 0660

Rated current: up to 1600 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 185 mm

Bar accommodation without inserts: 80 x 10 mm

Tightening torques

Assembly screws: 3 - 5 Nm

Bar fastening screw: 40 Nm