



Rittal – The System.

Faster – better – everywhere.



RX 9360.802

RiLineX bus-mounting fuse base

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.802 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.



Features

Obj. č.	RX 9360.802
Výhody	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Product modification	(sekundárne)
Materiál	Polyamid (PA 6) Správanie sa pri požiari podľa UL 94-V0
Farba	RAL 35745 RAL 9005
Rozsah dodávky	4 bus-mounting fuse bases 12 reducers for D 01 fuses

Features

Spôsob (elektrického) pripojenia	Spring terminal
Menovitý prúd max.	63 A
Menovité prevádzkové napätie	400 V AC
Vývod vodičov	Bottom
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 26,8 mm Výška: 253,8 mm Hĺbka: 89,8 mm
Pripojenie okrúhlych vodičov	16 mm ²
Vhodné pre prípojnice	Výška: 5, 10 mm
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	1 000 V
Stratový výkon max.	5,5 W
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Utilisation category	AC-21B (400 V/100 A)
Poistkové vložky	D 02-E 18

Features

Balenie	4 pc(s).
Netto hmotnosť	1,432 kg
Brutto hmotnosť	1,437 kg
Podiel medi (kg / ks)	0,07
PCF per pack (cradle-to-gate)	9,55
Číslo colnej sadzby	85369095
ETIM 9	EC001644

Popis výrobku	RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With optical LED fuse monitoring. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm ² at an angle of 45° allows easier conductor connection. The device is suitable for tool-free, snap-on mounting and features semi-automatic busbar adjustment for 5 and 10 mm.
---------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	----------------------------------------------