

**Rittal – The System.**

Faster – better – everywhere.



**RX 9360.805**

**RiLineX bus-mounting fuse base**

State: 23.5.2026 (Source: [rittal.com/sk-sk](http://rittal.com/sk-sk))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.805 - RiLineX bus-mounting fuse base

RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With electronic and optical LED fuse monitoring via alarm contacts. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm<sup>2</sup> at an angle of 45° allows easier conductor connection. The device is suitable for tool-free snap-on mounting and has semi-automatic rail adjustment for 5 and 10 mm.



## Features

Obj. č.	RX 9360.805
Výhody	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm <sup>2</sup> Complete contact hazard protection without any additional accessories (such as screw caps)
Product modification	(sekundárne)
Materiál	Polyamid (PA 6) Správanie sa pri požiari podľa UL 94-V0
Farba	RAL 35745 RAL 9005
Rozsah dodávky	4 bus-mounting fuse bases 12 reducers for D 01 fuses

# Features

Spôsob (elektrického) pripojenia	Spring terminal
Menovitý prúd max.	63 A
Menovité prevádzkové napätie	400 V AC
Vývod vodičov	Bottom
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 35,8 mm Výška: 253,8 mm Hĺbka: 89,8 mm
Pripojenie okrúhlych vodičov	16 mm <sup>2</sup>
Vhodné pre prípojnice	Výška: 5, 10 mm
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	1 000 V
Stratový výkon max.	5,5 W
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Utilisation category	AC-21B (400 V/100 A)
Poistkové vložky	D 02-E 18

# Features

---

Balenie	4 pc(s).
Netto hmotnosť	1,796 kg
Brutto hmotnosť	1,8 kg
Podiel medi (kg / ks)	0,07
PCF per pack (cradle-to-gate)	12,02
Číslo colnej sadzby	85369095
ETIM 9	EC001644

---

Popis výrobku	RiLineX bus-mounting fuse base for 60 mm busbar systems. For slow fuse D 01 (with gauge ring) and D 02 (E18). With electronic and optical LED fuse monitoring via alarm contacts. For reliable fuse contacting, the device has fuse holders instead of screw caps which are lockable the open state and sealable in the closed state. A spring terminal block up to 16 mm <sup>2</sup> at an angle of 45° allows easier conductor connection. The device is suitable for tool-free snap-on mounting and has semi-automatic rail adjustment for 5 and 10 mm.
---------------	---

# Approvals

---

Explanations	Declaration of conformity PCF-declaration
--------------	--