

Rittal – The System.

Faster – better – everywhere.



SK 3108.024 Enclosure internal fan

State: 06.04.2026 (Source: rittal.com/ua-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3108.024 - Enclosure internal fan

To prevent hot-spots inside the enclosure and support the air routing of active enclosure climate control components.



Features

Model No.	SK 3108.024
Product description	To prevent hot-spots and support the air routing of active enclosure climate control components. Adjustable in two axes. Attached to the frame section. Several fans may be cascaded using the quick-release clamping strip.
Supply includes	Complete unit with axial fan ready for connection Snap-on pivot device Assembly parts
Rated operating voltage	24 V (DC)
Power consumption Pel	With DC: 3.5 W
Rated current max.	With DC: 0.15 A
Packs of	1 pc(s).
Net weight	0.8 kg
Gross weight	0.978 kg
Customs tariff number	84145915
ETIM 9	EC000320
ETIM 8	EC000320

Features

ECLASS 8.0

27180716

Product description

SK enclosure internal fan, 3.5 W, 24 V (DC)

Approvals

Explanations

Declaration of conformity