

Rittal – The System.

Faster – better – everywhere.



RX 9364.024

RiLineX bus-mounting fuse base

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9364.024 - RiLineX bus-mounting fuse base

Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylindrical fuse 10 x 38 mm with electronic and optical LED fuse monitoring via alarm contacts. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 6 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.



Features

Obj. č.	RX 9364.024
Výhody	Reliable contacting of fuse inserts (without screw caps) Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) Optical LED fuse monitoring Voltage test through separate opening Maintenance-free tension spring connection up to 16 mm ² Complete contact hazard protection without any additional accessories (such as screw caps)
Product modification	(sekundárne)
Materiál	Polyamid (PA 6) Správanie sa pri požiari podľa UL 94-V0
Farba	RAL 35745 RAL 9005
Spôsob (elektrického) pripojenia	Spring terminal

Features

Menovitý prúd max.	32 A
Menovité prevádzkové napätie	400 V AC
Vývod vodičov	Bottom
Počet pólov	3-pole
Vhodné pre prípojnicový systém	RiLineX RiLine60
Rozmery	Šírka: 26,8 mm Výška: 262,5 mm Hĺbka: 95 mm
Pripojenie okrúhlych vodičov, jemne lankových s lisovacou dutinkou	1,5 - 6 mm ²
Pripojenie okrúhlych vodičov, jemne lankových s lisovacími dutinkami AWG	AWG 16 - AWG 6
Pripojenie okrúhlych vodičov, viacžilové	1,5 - 6 mm ²
Pripojenie okrúhlych vodičov, lankových AWG	AWG 16 - AWG 10
Vhodné pre prípojnice	15 x 5/10 20 x 5/10 30 x 5/10
Rated voltage	400 V AC
Trieda prepätia	4
Stupeň znečistenia	3
Normy	IEC/DIN EN 60 947-3
Rated insulation voltage Ui	800 V
Stratový výkon max.	3 W
Stupeň krytia IP podľa normy IEC 60 529	IP 2XB
Maximum operating air humidity	90 %

Features

Rozsah prevádzkových teplôt	-5 °C...55 °C
Rozsah skladovacích teplôt	-25 °C...75 °C
Vlhkosť vzduchu (nekondenzujúca)	10...90 %
Utilisation category	AC-20B (400 V/100 A)
Poistkové vložky	10 x 38 mm
Balenie	4 pc(s).
Netto hmotnosť	1,4 kg
Brutto hmotnosť	1,412 kg
Podiel medi (kg / ks)	0,043
PCF per pack (cradle-to-gate)	9,36
Číslo colnej sadzby	85369095
ETIM 9	EC001644
Popis výrobku	Compact RiLineX bus-mounting fuse base for 60 mm busbar systems. For cylindrical fuse 10 x 38 mm with electronic and optical LED fuse monitoring via alarm contacts. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 16 mm ² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm.

Approvals

Explanations	Declaration of conformity PCF-declaration
--------------	--