

Rittal – The System.

Faster – better – everywhere.



SV 9677.910 Pripojovacie bloky

State: 10.7.2026 (Source: rittal.com/sk-sk)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.910 - Pripojovacie bloky

For connecting cables and laminated copper bars.

Features

Obj. č.	SV 9677.910
Materiál	Oceľový plech, pozinkovaný E-Cu, pocínované
Výška upínacieho priestoru	20 mm
Šírka upínacieho priestoru	80 mm
Vývod vodičov	Top/bottom
Menovitý prúd max.	1 600 A
Rozmery	Šírka: 98 mm
Vhodné pre prípojnice	Výška: 10 mm
Balenie	1 pc(s).
Netto hmotnosť	0,9 kg
Brutto hmotnosť	0,982 kg
Podiel medi (kg / ks)	0,689
PCF per pack (cradle-to-gate)	3,7 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	85369095
ETIM 9	EC002270
ECLASS 8.0	27400613
Popis výrobku	SV pripojovací blok, 1600 A, 690 V, 1-pólový, vývod kábla hore/dole, upínací priestor ŠxV: 80x20 mm

Approvals

Approvals

UL + C-UL (listed)

Explanations

Declaration of conformity

Declaration of conformity UK