


Rittal – The System.

Faster – better – everywhere.



IT 7100.120 OCP ORV3 rack

状态: 2025/5/1 (来源: rittal.com/tw-zh)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 7100.120 - OCP ORV3 rack

OCP is an ambitious international community that aims to simplify and optimise IT infrastructure. The Rittal OCP ORV3 rack is OCP accepted and ready for immediate use. Simple modifications and enhancements can be made as and when required, thanks to the range of accessories. The OCP ORV3 rack can also accommodate a Direct Liquid Cooling (DLC) solution. Take your efficiency and performance density to a whole new level with this rack.



特征

型号	IT 7100.120
型式	Open frame Prepared for cable entry in roof and base Cable routing at the front, across the full height

特征

您的获益	<p>OCP ORV3 rack open on all sides and in line with Standard V3 of the OCP Community</p> <p>Prepared to accommodate 21" OCP components and direct contact on the busbar</p> <p>Rapid construction and service thanks to click-in fitting of the IT and IT OCP Power rail system</p> <p>End-to-end cable management in front rack over full height</p> <p>Ideal for high-performance computing and AI technology thanks to being ready for Direct Liquid Cooling solutions that are designed to dissipate the thermal load generated in the rack</p> <p>承载力高达1400 kg</p> <p>Integrated heavy-duty castors make transportation easier and ensure ease of handling in the data centre</p>
技术数据	Rated operating voltage: 48 V DC / power consumption 18 kW
材料	钢板
表面	浸涂底漆，外经粉末涂层
颜色	RAL 9005
供货范围	<p>OCP ORV3 rack</p> <p>OCP busbar for max. 48 DC/18 kW</p> <p>2 bracing struts, pre-assembled</p> <p>Levelling feet, pre-assembled</p> <p>4 castors (freely rotating)</p> <p>并柜密封胶条</p> <p>空气导流板</p>
尺寸	<p>宽度: 600 mm</p> <p>高度: 2,286 mm</p> <p>深度: 1,068 mm</p>
高度单位	44 OU
承载力	14,000 N

特征

基本材料	钢板
包装单元	1 件
净重	172
毛重	200
税率号	94032080
EAN	4028177997738
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207

批准

批准	IEC CB UL + C-UL (listed)
解释	符合性声明