

# Rittal – The System.

Faster – better – everywhere.



## SK 3235.440 EC speed control

State: 07.08.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3235.440 - EC speed control Control unit for EC fan

Temperature-dependent speed control for EC fan-and-filter units to reduce noise and save energy.

## Features

Model No.	SK 3235.440
Product description	Temperature-dependent speed control for EC fans to reduce noise and save energy. The function of the fan can also be monitored.
Function principle	Activation and monitoring of up to 4 EC filter fans For mounting on a 35 mm support rail EN 50 022 External temperature sensor to record the actual temperature Status LED to display the operating status Alarm relay for reporting overtemperature, fan defect, cable break and sensor failure
Supply includes	Speed control NTC sensor, length 1.80 m
Packs of	1 pc(s).
Speed	100 %
To fit Model No.	3140.500 3140.510 3240.500 3241.500 3243.500 3244.500 3245.500 3245.510 3245.508 3245.518
Setting range	5 °C...55 °C
Rated operating voltage	100 V – 250 V, 50 Hz/60 Hz
Net weight	0.45
Gross weight	0.51

# Features

Customs tariff number	90328900
EAN	4028177670716
ETIM 9	EC000256
ETIM 8	EC000256
ECLASS 8.0	27142320

# Approvals

Approvals	C-UR UR UR + C-UR (recognized)
Certificates	EAC
Explanations	Declaration of conformity