

# Rittal – The System.

Faster – better – everywhere.



## SK 3305.130

## Wall-mounted cooling units

State: 18.07.2025 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3305.130 - Wall-mounted cooling units with Basic controller

Wall-mounted cooling units in power categories 500 W to 4000 W with Basic controller integrated as standard, RiNano coating on the condenser and electrical condensate evaporation.



## Features

Model No.	SK 3305.130
Material	Sheet steel
Supply includes	Fully wired ready for connection Drilling template Assembly parts
Total cooling output to DIN EN 14511	Cooling output L35 L35/50 Hz: 1,500 W Cooling output L35 L35/60 Hz: 1,510 W Cooling output L35 L50/50 Hz: 850 W Cooling output L35 L50/60 Hz: 1,020 W
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated current max.	At 50 Hz: 5.6 A At 60 Hz: 6.2 A
Start-up current max.	At 50 Hz: 22 A At 60 Hz: 24 A
Air throughput (unimpeded air flow)	External circuit: 900 m³/h Internal circuit: 800 m³/h
Energy efficiency ratio (EER) 50/60 Hz L35 L35	Refrigeration factor L35 L35 (EER) 50 Hz: 1.8
Design	wall-mounted

# Features

Dimensions	Width: 400 mm Height: 950 mm Depth: 260 mm
Protection category to IEC 60 529	External circuit IP 34 Internal circuit IP 54
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.6 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 0.86 t
Temperature control	Basic controller (factory setting +35 °C)
Operating temperature range	20 °C...55 °C
Setting range	30 °C...55 °C
Power consumption Pel	Power consumption L35 L35/50 Hz: 850 W Power consumption L35 L35/60 Hz: 1,000 W Power consumption L35 L50/50 Hz: 1,000 W Power consumption L35 L50/60 Hz: 1,160 W
Pre-fuse	Miniature circuit-breaker/fuse: 16...16 A
Packs of	1 pc(s).
EAN	4028177560208
ECLASS 8.0	27180704

# Approvals

Certificates	EAC
Explanations	Declaration of conformity Declaration of conformity UK