Rittal - The System.

Faster – better – everywhere.





SK 3312.810 Wall-mounted cooling unit Blue e+

State: 20.11.2025 (Source: rittal.com/ua-en)



SK 3312.810 - Wall-mounted cooling unit Blue e+ IT

The use of Blue e+ technology makes this bundle ideally suited to the requirements of energy-efficient cooling of IT racks. In combination with the IoT interfaces, it supports communication with various systems as well as monitoring and energy management.

Features

| Model No. | SK 3312.810 |
|-------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Design | wall-mounted |
| Product description | The use of Blue e+ technology makes this bundle ideally suited to the requirements of energy-efficient cooling of IT racks. In combination with the IoT interfaces, it supports communication with various systems as well as monitoring and energy management. |
| Benefits | Energy savings thanks to speed-regulated components and heat pipe technology Suitable for international use due to a unique multi-voltage capability Intuitive operation due to touch display and intelligent interfaces |
| Technical specifications | Further information, instructions and technical data on the individual components listed in this bundle can be found on the relevant item pages |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Supply includes | Bundle comprised of the following individual components: loT interface (3124.300) Temperature sensor (3124.400) Connection cable (7030.091) Nylon loop cable holder (7111.350) Wall-mounted cooling unit (3187.930) |
| Useful cooling output L22 L30 | 3,000 W |
| Rated operating voltage | 110 V - 240 V, 1~, 50 Hz/60 Hz 380 V - 480 V, 3~, 50 Hz/60 Hz |
| Rated power input | 1.05 kW |

© Rittal 2025 2

Features

| Type of electrical connection | Plug-in terminal strip |
|------------------------------------------|--------------------------------------------------|
| Dimensions | Width: 450 mm |
| | Height: 1,600 mm |
| | Depth: 294 mm |
| Duty cycle | 100 % |
| Temperature control | e+ controller |
| Protocols | OPC-UA |
| | SNMPv1 |
| | SNMPv2 |
| | SNMPv3 |
| | Modbus/TCP |
| | TCP/IPv4 |
| | TCP/IPv6 |
| | Radius |
| | Telnet |
| | SSH |
| | FTP |
| | SFTP |
| | HTTP |
| | HTTPS |
| | NTP |
| | DHCP |
| | DNS |
| | SMTP |
| | Syslog |
| | LDAP |
| Operating temperature range | -20 °C60 °C |
| Permissible operating pressure (p. max.) | 25 bar |
| Storage temperature range | -40 °C70 °C |
| Setting range | 20 °C50 °C |
| Protection category to IEC 60 529 | External circuit IP 24 Internal circuit IP 55 |
| | |

© Rittal 2025 3

Features

| Refrigerant/cooling medium | Refrigerant: R-513A Quantity: 1.07 kg Global Warming Potential (GWP): 631 CO2 equivalent (CO2e): 0.68 t |
|----------------------------|------------------------------------------------------------------------------------------------------------------|
| Packs of | 1 pc(s). |
| Net weight | 69 |
| Gross weight | 74.5 |
| Customs tariff number | 84158200 |
| EAN | 4028177944558 |
| ETIM 9 | EC000855 |
| ETIM 8 | EC000855 |
| ECLASS 8.0 | 27180704 |

Approvals

|--|

© Rittal 2025