Rittal – The System.

Faster – better – everywhere.





HD 1682.600 Switch housing HD


State: 05.11.2025 (Source: rittal.com/ua-en)




HD 1682.600 - Switch housing HD

Enclosure solution with two cut-outs for switches, tailored to the requirements of the food and beverage industry. All-round gap-free silicone seal between enclosure and cover. Hygiene-compliant quick-release hexagon fastener.







Features

Model No.	HD 1682.600
Design	Hygienic Design enclosure
Material	Enclosure and cover: Stainless steel 1.4301 (AISI 304) 1.5 mm Screw plug: Stainless steel Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Enclosure and cover: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Enclosure of all-round solid construction Cover with switch cut-out Seal and screw plug (supplied loose)
Dimensions	Width front: 100 mm Width (rear): 122 mm Height, front: 160 mm Height rear: 182 mm Depth: 90 mm
Pitch pattern	60 mm
Cut-outs (quantity x diameter)	2 x 22.5 mm

© Rittal 2025 2

Features

IK Code	IK08
Basic material	Stainless steel 1.4301 (AISI 304)
Lock	Lock version: Hygiene-compliant quick-release hexagon fastener Number of locks: 4
IP protection category to IEC 60	IP 66
529	IP X9
Protection category NEMA	NEMA 1
	NEMA 3
	NEMA 3X
	NEMA 4
	NEMA 4X
	NEMA 12
	NEMA 13
Type rating to UL 50E	Type 1
	Type 3
	Type 3X
	Type 4
	Type 4X
	Type 12
	Type 13
Packs of	1 pc(s).
Net weight	1.1
Gross weight	1.3
Customs tariff number	84879090
EAN	4028177958678
ETIM 9	EC000261
ETIM 8	EC002713
ECLASS 8.0	27180101

Approvals

© Rittal 2025 3

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

Tender text

HD Switch housing

Enclosure consisting of body and cover. Body folded and welded in one piece, with all-round, removable blue silicone seal compliant to FDA-quidline 21 CFR 177.2600 body tilted by 3° for optimum cleaning, in accordance with EHEDG guidlines. Cover on top, tilted by 3° with two cut-outs each 22.5 mm for two switches four hygienic hexagonal screw plugs with all-round sealing ring between enclosure and cover,

protective conductor connection in cover and body

Material:

Body and cover: stainless steel 1.4301 (AISI 304) 1,5 mm

Screw plug: stainless steel

Seal: silicone, compliant with FDA guidline 21 CFR 177.2600

Surface finish:

Body and cover: brushed, grain 400,

peak-to-valley height: < 0,8 µm Seal: blue, dyed (RAL 5010)

Protection class IP according to IEC 60 529: IP 66, IPX9

Type rating according to UL 50E: Type 13, 3R, 4X

Model No.: 1682600

Dimensions (W x H x D): 100 x 160 x 90 mm

© Rittal 2025 4