

Rittal – The System.

Faster – better – everywhere.



SG 2369.010

Steady light component

State: 05.06.2025 (Source: [rittal.com/ua-en](https://www.rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2369.010 - Steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system, number of potential stages = 5 components, with identical voltage.

Features

| | |
|---|--|
| Model No. | SG 2369.010 |
| Design | Steady light component |
| Product description | With 360° signal transmission thanks to optimised prism system. No. of potential stages = 5 components, with identical voltage. |
| Benefits | Simple assembly and contact via bayonet fastener. Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages. |
| Function principle | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel |
| Material | Enclosure of polyamide Cap: Transparent polycarbonate |
| Colour | Green |
| Diameter | 70 mm |
| Rated impulse withstand voltage, phase to phase | 2500 V AC |
| Rated insulation voltage | 250 V AC |
| Note on Model No. | Incandescent lamps not included with the supply. |
| Dimensions | Height: 56 mm |
| Protection category to IEC 60 529 | IP 54 if a cover or acoustic component is fitted at the top |
| Rated operating voltage | 12 V - 240 V (AC/DC) |
| Packs of | 1 pc(s). |
| Net weight | 0.07 |
| Gross weight | 0.087 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85311095 |
| EAN | 4028177219939 |
| ECLASS 8.0 | 27371220 |

Approvals

| | |
|-----------|--------------------------|
| Approvals | UL + C-UL (listed) UR |
|-----------|--------------------------|