

**Rittal – The System.**

Faster – better – everywhere.



**AX 2393.210**

**Rail for interior installation AX**

State: 11.05.2026 (Source: [rittal.com/ua-en](http://rittal.com/ua-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2393.210 - Rail for interior installation AX

For mounting in the enclosure, no machining required. Suitable for mounting on the side, base and roof up to a load of 25 N using the locators integrated into the enclosure.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | AX 2393.210  |
| Product description   | For mounting in the enclosure, no machining required. Suitable for mounting on the side, base and roof up to a load of 25 N using the locators integrated into the enclosure lights, door-operated switch, door stay, cable conduit holder enclosure. Variable with 2 rows of system punchings, creates additional mounting space e.g. for:<br>Punched section with mounting flange 14 x 39 mm, enclosure lights, door-operated switch, door stay, cable conduit holder. |
| Benefits              | Only one screw for attaching the rail inside the enclosure<br>Including adaptor for door-operated switch<br>Compatibility with VX25 accessories<br>Enclosure protection category is retained (no machining required)<br>Automatic potential equalisation<br>May be retro-fitted even with the mounting plate in situ. Suitable for installation via gland plates   |
| Material              | Sheet steel  |
| Surface finish        | Zinc-plated  |
| Assembly instruction  | For installing LED system light, only in conjunction with mounting bracket for interior installation   |
| To fit                | Enclosure type: AX<br>Depth: = 210 mm  |
| Packs of              | 4 pc(s).   |
| Net weight            | 0.536 kg   |
| Gross weight          | 0.632 kg   |
| Customs tariff number | 73269098   |
| ECLASS 8.0            | 27189234   |
| Product description   | AX Rail for interior installation, for D: 210 mm   |