## Rittal – The System.

Faster - better - everywhere.





# SV 3052.000 Busbar support

State: 04.11.2025 (Source: rittal.com/ua-en)



## SV 3052.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).

### **Features**

Model No.	SV 3052.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT)
	Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole
	185 mm
To fit busbars	50 x 10
	60 x 10
	80 x 10
Rated current max.	1,600 A
Note on Model No.	The base component of the busbar support may also be used as a
	single-pole support.
Dimensions	Width: 24 mm
	Height: 515 mm
	Depth: 51 mm
Packs of	2 pc(s).
Net weight	1.26
Gross weight	1.338
Customs tariff number	85369010
EAN	4028177035751
ETIM 9	EC001166
ETIM 8	EC001166
ECLASS 8.0	27400607

© Rittal 2025

### **Approvals**

Approvals	ABS	
Explanations	Declaration of conformity	
	Declaration of conformity UK	

#### Tender text

SV busbar support for accommodating busbars. 3-pole busbar support with 185 mm bar centre distance.
Suitable for busbars from 50 x 10 mm to 80 x 10 mm with inserts.

Rated operating voltage: 1000 V~, 50/60 Hz to VDE 0660

Rated current: up to 1600 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 185 mm

Bar accommodation without inserts: 80 x 10 mm

Tightening torques

Assembly screws: 3 - 5 Nm Bar fastening screw: 40 Nm

© Rittal 2025 3