
Rittal – The System.

Faster – better – everywhere.





SK 3149.410 TopTherm roof-mounted fans

State: 17.11.2025 (Source: rittal.com/ua-en)



SK 3149.410 - TopTherm roof-mounted fans for TS 8

The roof-mounted fans for TS fit precisely onto the cut-outs of the TopTherm roof-mounted cooling units. Also suitable for mounting on any sufficiently large roof surface. Mounting cut-outs are not compatible with successor products in the VX IT family. If reusing the roof plate in the VX IT, adaptor frame 5050.701 will be required.

Features

Model No.	SK 3149.410	
Product description	The active roof-mounted fans fit precisely onto the cut-outs of the small and medium performance category of TopTherm roof-mounted cooling units.	
Product modification	Монтажные вырезы не совместимы. При последующем использовании потолочной панели необходима адаптерная рама 5050.701. Mounting cut-outs are not compatible. If reusing the roof plate, adaptor frame 5050.701 is required.	
Material	Sheet steel, spray-finished	
Colour	RAL 7035	
Supply includes	Unit ready for connection with built-in radial fan Sealing and assembly parts	
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz	
Power consumption Pel	At 50 Hz: 120 W At 60 Hz: 170 W	
Rated current max.	At 50 Hz: 1.1 A At 60 Hz: 1.6 A	
Dimensions	Width: 550 mm Height: 125 mm Depth: 370 mm	
Mounting cut-out	Cut-out width: 475 mm Cut-out depth: 260 mm	
IP protection category to IEC 60 529	IP 43	

© Rittal 2025 2

Features

Operating temperature range	-10 °C55 °C
Noise level	At 50 Hz: 68 dB(A) At 60 Hz: 69 dB(A)
Packs of	1 pc(s).
Net weight	9.031
Gross weight	9.506
Customs tariff number	84145915
EAN	4028177387119
ECLASS 8.0	27180716

Approvals

·	D 1 11 (()
Explanations	Declaration of conformity

© Rittal 2025 3