


Rittal – The System.

Faster – better – everywhere.



SV 3456.500

Conductor connection clamp

State: 10.02.2026 (Source: rittal.com/ua-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 3456.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

Model No.	SV 3456.500
Product description	For connecting round conductors and laminated copper bars.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	8 x 8 mm
Note	Wire end ferrules should be used with fine wire conductors
Connection of round conductors	2.5 - 16 mm ²
For bar thickness	10 mm
Packs of	15 pc(s).
Net weight	0.405
Gross weight	0.45
PCF per pack (cradle-to-gate)	1.7 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	85369010
EAN	4028177042742
ETIM 9	EC000001
ETIM 8	EC000001
ECLASS 8.0	27141146

Approvals

Approvals	UR + C-UR (recognized)
Explanations	Declaration of conformity Declaration of conformity UK

Tender text

SV conductor connection clamps
for E-CU busbars and Rittal PLS.
For bar thickness: 10 mm
Connection of round conductors: 2.5 - 16 mm²
Wire end ferrules should be used with
fine wire conductors.
Clamping area:,,
for lam. copper bars 8 x 8 mm
Tightening torque
Conductor connection clamp: 3 Nm
Material: sheet steel, zinc plated, passivated